



LF3006009001



Trunking from PVC LF 30x60mm cream white

Technical properties

Connectivity

Trunking coupling Pre-equipped with couplers

Dimensions

Trunking height 30 mm

Length 2000 mm

Trunking width 57 mm

Distance bottom-punch along trunking-direction 125 mm

Distance bottom-punch crosswise trunking-direction 18 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 7

Maximum number of cables (Ø 11 mm, 50% fill) 7

Cover, door

Lid shape loose

Materials

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Internal/useful cross section 1500 mm²

Equipment

Number of fix dividers 0

Number of plugable separators 0

Compartment quantity 1

Cable retainers per meter 2

Standards

Approvals EN50085-2-1

European directive RoHs voluntary compliance

temperatur

Ambient temperature -5...65 °C