



LF4004009001



Trunking from PVC LF 40x40mm cream white

Technical properties

Connectivity

Trunking coupling Pre-equipped with couplers

Dimensions

| | |
|--|---------|
| Trunking height | 40 mm |
| Length | 2000 mm |
| Trunking width | 40 mm |
| Distance bottom-punch along trunking-direction | 125 mm |

Capacity

| | |
|--|---|
| Maximum number of cables (Ø 11 mm, 50% fill) | 6 |
| Maximum number of cables (Ø 11 mm, 50% fill) | 6 |

Cover, door

Lid shape loose

Materials

| | |
|---------------------------|-----------|
| Material group | plastic |
| Type of surface treatment | untreated |
| Transparent | No |

Cable

Internal/useful cross section 900 mm²

Equipment

| | |
|-------------------------------|---|
| Number of fix dividers | 0 |
| Number of plugable separators | 0 |
| Compartment quantity | 1 |
| Cable retainers per meter | 0 |

Standards

| | |
|-------------------------|----------------------|
| Approvals | EN50085-2-1 |
| European directive RoHs | voluntary compliance |

temperatur

Ambient temperature -5...65 °C