



LF4009007030



**Trunking from PVC LF 40x90mm stone grey**

**Technical properties**

**Architecture**

Fixing mode bottom punched

**Configuration**

Antibacterial treatment No

**Connectivity**

Trunking coupling Pre-equipped with couplers

**Dimensions**

Trunking height 40 mm

Length 2000 mm

Trunking width 90 mm

Distance bottom-punch along trunking-direction 125 mm

Distance bottom-punch crosswise trunking-direction 50 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 10

Maximum number of cables (Ø 11 mm, 50% fill) 10

**Cover, door**

Lid shape loose

**Materials**

Colour stone grey

RAL colour RAL 7030 - Stone grey

Material PVC

Material group plastic

Type of surface treatment untreated

Transparent No

**Cable**

Internal/useful cross section 2400 mm<sup>2</sup>

**Equipment**

Number of plugable separators 1

Compartment quantity 1 / 2

Cable retainers per meter 2

**Standards**

---

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

---

**Safety**

---

Protection index IP	IP30
Impact strength	IK07

---

**Use conditions**

---

Operating temperature	-5...60 °C
-----------------------	------------

---

**temperatur**

---

Ambient temperature	-5...65 °C
---------------------	------------

---