



LF4009007030



Trunking from PVC LF 40x90mm stone grey

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

Dimensions

Trunking height	40 mm
Length	2000 mm
Trunking width	90 mm
Distance bottom-punch along trunking-direction	125 mm
Distance bottom-punch crosswise trunking-direction	50 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	10
Maximum number of cables (Ø 11 mm, 50% fill)	10

Cover, door

Lid shape	loose
-----------	-------

Materials

Material group	plastic
Type of surface treatment	untreated
Transparent	No

Cable

Internal/useful cross section	2400 mm ²
-------------------------------	----------------------

Equipment

Number of pluggable separators	1
Compartment quantity	1 / 2
Cable retainers per meter	2

Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
Halogen free	No
Impact strength	IK07
Use conditions	
Operating temperature	-5...60 °C
temperatur	
Ambient temperature	-5...65 °C