



LF6006009010



**Trunking from PVC LF 60x60mm pure white**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Connectivity**

Trunking coupling Pre-equipped with couplers

**Dimensions**

Trunking height 60 mm

Length 2000 mm

Trunking width 57 mm

Distance bottom-punch along trunking-direction 125 mm

Distance bottom-punch crosswise trunking-direction 28 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 12

Maximum number of cables (Ø 11 mm, 50% fill) 12

**Cover, door**

Lid shape loose

**Materials**

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

Transparent No

**Cable**

Internal/useful cross section 2690 mm<sup>2</sup>

**Equipment**

Number of fix dividers 0

Number of plugable separators 1

Compartment quantity 1 / 2

Cable retainers per meter 2

**Standards**

Approvals EN50085-2-1

European directive RoHS voluntary compliance

---

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

---

**Use conditions**

Operating temperature	-5...60 °C
-----------------------	------------

---

**temperatur**

Ambient temperature	-5...65 °C
---------------------	------------