



LF6009007030



Trunking from PVC LF 60x90mm stone grey

Technical properties

Architecture

Fixing mode bottom punched

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling Pre-equipped with couplers

Dimensions

Trunking height 60 mm

Length 2000 mm

Trunking width 90 mm

Distance bottom-punch along trunking-direction 125 mm

Distance bottom-punch crosswise trunking-direction 50 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 18

Maximum number of cables (Ø 11 mm, 50% fill) 18

Cover, door

Lid shape loose

Materials

Colour stone grey

RAL colour RAL 7030 - Stone grey

Material PVC

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Internal/useful cross section 4360 mm²

Equipment

Number of plugable separators 1

Compartment quantity 1 / 2

Cable retainers per meter 2

Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP30
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------
