



LF6011007030



Trunking from PVC LF 60x110mm stone grey

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling Pre-equipped with couplers

Dimensions

Trunking height 60 mm

Length 2000 mm

Trunking width 110 mm

Distance bottom-punch along trunking-direction 125 mm

Distance bottom-punch crosswise trunking-direction 80 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 23

Maximum number of cables (Ø 11 mm, 50% fill) 23

Cover, door

Lid shape loose

Materials

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Internal/useful cross section 5460 mm²

Equipment

Number of plugable separators 3

Compartment quantity 1 / 4

Cable retainers per meter 2

Standards

Approvals EN50085-2-1

European directive RoHs voluntary compliance

Safety

REACH conform Yes

RoHS conform	Yes
Halogen free	No
Impact strength	IK07
Use conditions	
Operating temperature	-5...60 °C
temperatur	
Ambient temperature	-5...65 °C