



LF6011007030



**Trunking from PVC LF 60x110mm stone grey**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Connectivity**

Trunking coupling Pre-equipped with couplers

**Dimensions**

Trunking height 60 mm

Length 2000 mm

Trunking width 110 mm

Distance bottom-punch along trunking-direction 125 mm

Distance bottom-punch crosswise trunking-direction 80 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 23

Maximum number of cables (Ø 11 mm, 50% fill) 23

**Cover, door**

Lid shape loose

**Materials**

Colour stone grey

Material group plastic

Type of surface treatment untreated

Transparent No

**Cable**

Internal/useful cross section 5460 mm<sup>2</sup>

**Equipment**

Number of plugable separators 3

Compartment quantity 1 / 4

Cable retainers per meter 2

**Standards**

European directive RoHS voluntary compliance

**Safety**

Protection index IP IP30

**Use conditions**

---

Operating temperature

-5...60 °C

**temperatur**

---

Ambient temperature

-5...65 °C