



LFH6009009001



**Trunking halogen-free,60x90,craem white**

**Technical properties**

**Connectivity**

Trunking coupling Pre-equipped with couplers

**Dimensions**

Trunking height 60 mm

Length 2000 mm

Trunking width 90 mm

Distance bottom-punch along trunking-direction 125 mm

Distance bottom-punch crosswise trunking-direction 40 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 18

**Cover, door**

Lid shape loose

**Materials**

Material group plastic

Type of surface treatment untreated

Transparent No

**Cable**

Internal/useful cross section 4360 mm<sup>2</sup>

**Equipment**

Number of fix dividers 0

Number of plugable separators 1

Compartment quantity 1

Cable retainers per meter 2

**Standards**

Approvals EN50085-2-1

European directive RoHs voluntary compliance

**temperatur**

Ambient temperature -30...90 °C