



LNH0050M

HRC LV fuse NH000 gG AC500V 50A double indicator with live gripping-lugs

Technical properties

Architecture

Curve	gG
-------	----

Main electrical features

Rated short circuit breaking capacity I _{cn} AC according IEC60898-1	120 kA
Rated operational voltage U _e	500 V
Type of supply voltage	AC/DC

Voltage

Rated voltage DC	250 V
------------------	-------

Electric current

Cut off current	120 kA
Rated current	50 A

Fuse

CharactFuse	gG
Fuse Size	NH000

Dimensions

Depth of installed product	79 mm
Height of installed product	58.5 mm
Width of installed product	21 mm

Power

Total power loss under I _N	4.1 W
---------------------------------------	-------

Standards

Approvals	VDE, EAC
-----------	----------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Altitude	2000 m
Insulated	No

Identification

Device family	LNH
---------------	-----