



LNH0050M

**HRC LV fuse NH000 gG AC500V 50A double indicator with live gripping-lugs**

**Technical properties**

**Architecture**

Curve	gG
-------	----

**Main electrical features**

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	120 kA
Rated operational voltage $U_e$	500 V
Type of supply voltage	AC/DC

**Voltage**

Rated voltage DC	250 V
------------------	-------

**Electric current**

Cut off current	120 kA
Rated current	50 A

**Fuse**

CharactFuse	gG
Fuse Size	NH000

**Dimensions**

Depth of installed product	79 mm
Height of installed product	58.5 mm
Width of installed product	21 mm

**Power**

Total power loss under $I_N$	4.1 W
------------------------------	-------

**Standards**

Approvals	VDE, EAC
-----------	----------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Use conditions**

Altitude	2000 m
Insulated	No

**Identification**

Device family	LNH
---------------	-----