



LNH0100M

HRC LV fuse NH000 gG AC500V 100A double indicator with live gripping-lugs

Technical properties

Architecture

Curve	gG
-------	----

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	120 kA
Rated operational voltage U_e	500 V
Type of supply voltage	AC/DC

Voltage

Rated voltage DC	250 V
------------------	-------

Electric current

Cut off current	120 kA
Rated current	100 A

Fuse

CharactFuse	gG
Fuse Size	NH000

Dimensions

Depth of installed product	79 mm
Height of installed product	58.5 mm
Width of installed product	21 mm

Power

Total power loss under IN	7.5 W
---------------------------	-------

Standards

Approvals	VDE, EAC
-----------	----------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Altitude	2000 m
Insulated	No

Identification

Device family	LNH
---------------	-----