



LNH0100M

## HRC LV fuse NH000 gG AC500V 100A double indicator with live gripping-lugs

### Technical properties

#### Architecture

Curve	gG
-------	----

#### Main electrical features

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	120 kA
Rated operational voltage $U_e$	500 V
Type of supply voltage	AC/DC

#### Voltage

Rated voltage DC	250 V
------------------	-------

#### Electric current

Cut off current	120 kA
Rated current	100 A

#### Fuse

CharactFuse	gG
Fuse Size	NH000

#### Dimensions

Depth of installed product	79 mm
Height of installed product	58.5 mm
Width of installed product	21 mm

#### Power

Total power loss under $I_N$	7.5 W
------------------------------	-------

#### Standards

Approvals	VDE, EAC
-----------	----------

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Use conditions

Altitude	2000 m
Insulated	No

#### Identification

Device family	LNH
---------------	-----