



LNH0100M

HRC LV fuse NH000 gG AC500V 100A double indicator with live gripping-lugs

Technical properties

Main electrical features

|   |        |
|---|--------|
| Rated short circuit breaking capacity Icn AC according IEC60898-1 | 120 kA |
| Rated operational voltage Ue                                      | 500 V  |

Voltage

|                  |       |
|------------------|-------|
| Rated voltage DC | 250 V |
|------------------|-------|

Electric current

|                 |        |
|-----------------|--------|
| Cut off current | 120 kA |
| Rated current   | 100 A  |

Fuse

|           |       |
|-----------|-------|
| Fuse Size | NH000 |
|-----------|-------|

Dimensions

|                             |         |
|-----------------------------|---------|
| Depth of installed product  | 79 mm   |
| Height of installed product | 58.5 mm |
| Width of installed product  | 21 mm   |

Power

|                           |       |
|---------------------------|-------|
| Total power loss under IN | 7.5 W |
|---------------------------|-------|

Standards

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Use conditions

|           |        |
|-----------|--------|
| Altitude  | 2000 m |
| Insulated | No     |