



LNH0125M

HRC LV fuse NH00 gG AC500V 125A double indicator with live gripping-lugs

Technical properties

Architecture

Curve gG

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1 120 kA

Rated operational voltage U_e 500 V

Type of supply voltage AC/DC

Voltage

Rated voltage DC 250 V

Electric current

Cut off current 120 kA

Rated current 125 A

Fuse

CharactFuse gG

Fuse Size NH00

Dimensions

Depth of installed product 79 mm

Height of installed product 58.5 mm

Width of installed product 21 mm

Power

Total power loss under I_N 10 W

Standards

Approvals VDE, EAC

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Altitude 2000 m

Insulated No

Identification

Device family LNH