



LNH0160M

NH fuse NH00 gG 500V 160A central indicator live grippings

Technical properties

Architecture

Curve gG

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1 120 kA

Rated operational voltage U_e 500 V

Type of supply voltage AC/DC

Voltage

Rated voltage DC 250 V

Electric current

Cut off current 120 kA

Rated current 160 A

Fuse

CharactFuse gG

Fuse Size NH00

Dimensions

Depth of installed product 51 mm

Height of installed product 79 mm

Length 51 mm

Width of installed product 21 mm

Power

Total power loss under I_N 12 W

Standards

Approvals VDE, EAC

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Altitude 2000 m

Insulated No

Identification

