



LNH0160M

## NH fuse NH00 gG 500V 160A central indicator live grippings

### Technical properties

#### Architecture

Curve	gG
-------	----

#### Main electrical features

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	120 kA
Rated operational voltage $U_e$	500 V
Type of supply voltage	AC/DC

#### Voltage

Rated voltage DC	250 V
------------------	-------

#### Electric current

Cut off current	120 kA
Rated current	160 A

#### Fuse

CharactFuse	gG
Fuse Size	NH00

#### Dimensions

Depth of installed product	51 mm
Height of installed product	79 mm
Length	51 mm
Width of installed product	21 mm

#### Power

Total power loss under $I_N$	12 W
------------------------------	------

#### Standards

Approvals	VDE, EAC
-----------	----------

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Use conditions

Altitude	2000 m
Insulated	No

#### Identification

