



LNH1160M

HRC LV fuse NH1 gG AC500V 160A double indicator with live gripping-lugs

Technical properties

Architecture

Curve	gG
-------	----

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	120 kA
Rated operational voltage U_e	500 V
Type of supply voltage	AC/DC

Voltage

Rated voltage DC	250 V
------------------	-------

Electric current

Cut off current	120 kA
Rated current	160 A

Fuse

CharactFuse	gG
Fuse Size	NH1

Dimensions

Depth of installed product	135 mm
Height of installed product	64.5 mm
Width of installed product	135 mm

Power

Total power loss under I_N	14.6 W
------------------------------	--------

Standards

Approvals	VDE, EAC
-----------	----------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Altitude	2000 m
Insulated	No

Identification

Device family	LNH
---------------	-----