



LNH2250M

## NH fuse NH2C gG 500V 250A central indicator live gripping lugs

### Technical properties

#### Main electrical features

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	120 kA
Rated operational voltage $U_e$	500 V
Type of supply voltage	AC

#### Electric current

Cut off current	120 kA
Rated current	250 A

#### Dimensions

Depth of installed product	150 mm
Height of installed product	72.5 mm
Length	62 mm
Width of installed product	49 mm

#### Power

Total power loss under $I_N$	20.6 W
------------------------------	--------

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Altitude	2000 m
Insulated	No