


MZ206



Under voltage release 230V AC

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

Rated insulation voltage	4000 V
DC control voltage	0 V
Command voltage AC	230 V
Rated operational voltage in DC	0 V

Electric current

Acceptable current rating with AC1	15 mA
------------------------------------	-------

Dimensions

Depth of installed product	68 mm
Width of installed product	17.5 mm

Power

Inrush power absorbed	3.5 VA
Total power loss under IN	2 W

Tripping

Time of response when opening	200 ms
Performance voltage / Tripping at Ue	35 / 70 %

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-25...60 °C
Air humidity protection	95%
Storage/transport temperature	-40...80 °C