


MZ206



## Under voltage release 230V AC

### Technical properties

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Rated operational voltage $U_e$	230 V
Type of supply voltage	AC
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	4000 V
DC control voltage	0 V
Command voltage AC	230 V
Rated operational voltage in DC	0 V

#### Electric current

Acceptable current rating with AC1	15 mA
------------------------------------	-------

#### Dimensions

Depth of installed product	68 mm
Width of installed product	17.5 mm

#### Power

Inrush power absorbed	3.5 VA
Total power loss under IN	2 W

#### Tripping

Time of response when opening	200 ms
Performance voltage / Tripping at $U_e$	35 / 70 %

#### Connection

Connection cross-sect. flexible conductor	6mm <sup>2</sup>
---	------------------

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

#### Use conditions

Operating temperature	-25...60 °C
Air humidity protection	95%
Storage/transport temperature	-40...80 °C