




SK600



## Selector switch non spring ret

### Technical properties

#### Architecture

Number of poles	1 P
-----------------	-----

#### Configuration

Number of modules	3
-------------------	---

#### Controls and indicators

Number of positions of the switch	3
-----------------------------------	---

#### Main electrical features

Rated operational voltage $U_e$	660 V
---------------------------------	-------

Frequency	50 Hz
-----------	-------

#### Voltage

Rated insulation voltage	690 V
--------------------------	-------

#### Electric current

Rated current	20 A
---------------	------

#### Dimensions

Depth of installed product	64 mm
----------------------------	-------

Height of installed product	85 mm
-----------------------------	-------

Width of installed product	53 mm
----------------------------	-------

#### Power

Total power loss under IN	0.7 W
---------------------------	-------

#### Connection

Number of contacts	1
--------------------	---

#### Safety

Protection index IP	IP20
---------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

#### Use conditions

Operating temperature	-10...40 °C
-----------------------	-------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------