




SK600



**Selector switch non spring ret**

**Technical properties**

**Architecture**

Number of poles 1 P

**Configuration**

Number of modules 3

**Controls and indicators**

Number of positions of the switch 3

**Main electrical features**

Rated operational voltage  $U_e$  660 V

Frequency 50 Hz

**Voltage**

Rated insulation voltage 690 V

**Electric current**

Rated current 20 A

**Dimensions**

Depth of installed product 64 mm

Height of installed product 85 mm

Width of installed product 53 mm

**Power**

Total power loss under IN 0.7 W

**Connection**

Number of contacts 1

**Safety**

Protection index IP IP20

**Use conditions**

Operating temperature -10...40 °C

Storage/transport temperature -40...80 °C