




SK600



Selector switch non spring ret

Technical properties

Architecture

Number of poles 1 P

Configuration

Number of modules 3

Controls and indicators

Number of positions of the switch 3

Main electrical features

Rated operational voltage U_e 660 V

Frequency 50 Hz

Voltage

Rated insulation voltage 690 V

Electric current

Rated current 20 A

Dimensions

Depth of installed product 64 mm

Height of installed product 85 mm

Width of installed product 53 mm

Power

Total power loss under IN 0.7 W

Connection

Connection cross-sect. flexible conductor 1,5 / 10mm²

Connection cross-sect. rigid cable 1 / 6mm²

Number of contacts 1

Type of contacts NO-NC

Type of connection with screw

Safety

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -10...40 °C

Storage/transport temperature -40...80 °C