



SK604



## Changeover switch 4DIRo

### Technical properties

#### Configuration

Number of modules	3
-------------------	---

#### Controls and indicators

Number of positions of the switch	5
-----------------------------------	---

#### Main electrical features

Frequency	50 Hz
-----------	-------

#### Voltage

Rated insulation voltage	690 V
--------------------------	-------

#### Electric current

Rated current	20 A
---------------	------

#### Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	70 mm

#### Power

Total power loss under IN	1 W
---------------------------	-----

#### Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Use conditions

Operating temperature	-10...40 °C
Storage/transport temperature	-40...80 °C