



## Trunking 11x40, grey

### Technical properties

#### Configuration

Antibacterial treatment	No
Self-adhesive	No

#### Dimensions

Trunking height	11 mm
Length	2000 mm
Trunking width	40 mm
Width of installed product	40 mm

#### Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	1
Maximum number of cables (Ø 11 mm, 50% fill)	1

#### Cover, door

Lid with softlip	No
------------------	----

#### Materials

Material group	plastic
Type of surface treatment	untreated

#### Equipment

Compartment quantity	1
Number of channels	1

#### Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

#### temperatur

Ambient temperature	-5...65 °C
---------------------	------------

SL1104007030

