



SM020

## Digital ammeter 0-20A direct reading

### Technical properties

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Configuration

Number of modules	4
-------------------	---

#### Controls and indicators

Measurement scale	20 A
-------------------	------

#### Main electrical features

Rated operational voltage Ue	207 / 230 / 253 V
------------------------------	-------------------

#### Voltage

Voltage drop	120 mV
--------------	--------

#### Dimensions

Depth of installed product	54 mm
Height of installed product	85 mm
Width of installed product	70 mm

#### Power

Power consumed	1 VA
Total power loss under IN	1 W

#### Installation, mounting

Modular version	Yes
-----------------	-----

#### Connection

Connection cross-sect. flexible conductor	6mm <sup>2</sup>
---	------------------

#### Equipment

Digits number	3
---------------	---

#### Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Operating temperature	-10...55 °C
Storage/transport temperature	-40...70 °C