



SM101C

## Communicant Modular multifunction meter

### Technical properties

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Configuration

Number of modules	4
-------------------	---

#### Main electrical features

Rated operational voltage Ue	200 / 230 / 277 V
Frequency	50/60 Hz

#### Dimensions

Depth of installed product	50 mm
Height of installed product	45 mm
Length	67 mm
Width of installed product	73 mm

#### Power

Power consumed	5 VA
Total power loss under IN	5 W

#### Measurement

Frequency measuring range	45 to 65 Hz
Voltage measurement range	50 to 500 V
Type of measuring instrument	multimeter

#### Installation, mounting

Mounting type	din-Rail
---------------	----------

#### Connection

Type of connection	with screw
--------------------	------------

#### Equipment

Type of display	Digital
Digits number	4

#### Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Use conditions**

Operating temperature	-10...55 °C
Storage/transport temperature	-20...70 °C