



SM101C

Communicant Modular multifunction meter

Technical properties

Functions

Precision class	0.5%
-----------------	------

Configuration

Number of modules	4
-------------------	---

Main electrical features

Rated operational voltage Ue	200 / 230 / 277 V
------------------------------	-------------------

Frequency	50/60 Hz
-----------	----------

Dimensions

Depth of installed product	50 mm
----------------------------	-------

Height of installed product	45 mm
-----------------------------	-------

Length	67 mm
--------	-------

Width of installed product	73 mm
----------------------------	-------

Power

Power consumed	5 VA
----------------	------

Total power loss under IN	5 W
---------------------------	-----

Measurement

Frequency measuring range	45 to 65 Hz
---------------------------	-------------

Voltage measurement range	50 to 500 V
---------------------------	-------------

Type of measuring instrument	multimeter
------------------------------	------------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	0,5 / 4mm ²
---	------------------------

Connection cross-sect. rigid cable	0,5 / 4mm ²
------------------------------------	------------------------

Type of connection	with screw
--------------------	------------

Equipment

Type of display	Digital
-----------------	---------

Digits number	4
---------------	---

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Use conditions

Operating temperature	-10...55 °C
Storage/transport temperature	-20...70 °C
