



SM102E

## Multi-function measurement device

### Technical properties

#### Configuration

Number of modules	5
-------------------	---

#### Controls and indicators

Measurement scale	5 A
-------------------	-----

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Voltage

Rated insulation voltage	4 kV
--------------------------	------

#### Dimensions

Depth of installed product	60 mm
Height of installed product	96 mm
Length	80 mm
Width of installed product	96 mm

#### Power

Power consumed	10 VA
Total power loss under IN	10 W

#### Measurement

Frequency measuring range	45 to 65 Hz
Voltage measurement range	50 to 500 V
Type of measuring instrument	multimeter

#### Installation, mounting

Mounting type	flush mounted / surface mounted
---------------	---------------------------------

#### Connection

Connection cross-sect. flexible conductor	2,5 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	2,5 / 6mm <sup>2</sup>
Type of connection	with screw

#### Equipment

Type of display	LCD
Digits number	4

#### Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------

