



SM103E

Multi-function measurement device Evolution

Technical properties

Configuration

Number of modules	5
-------------------	---

Controls and indicators

Measurement scale	5 A
-------------------	-----

Main electrical features

Rated operational voltage Ue	110 / 230 / 400 V
------------------------------	-------------------

Frequency	50/60 Hz
-----------	----------

Voltage

Rated insulation voltage	4 kV
--------------------------	------

Dimensions

Depth of installed product	60 mm
----------------------------	-------

Height of installed product	96 mm
-----------------------------	-------

Length	80 mm
--------	-------

Width of installed product	96 mm
----------------------------	-------

Power

Power consumed	10 VA
----------------	-------

Total power loss under IN	10 W
---------------------------	------

Measurement

Frequency measuring range	45 to 65 Hz
---------------------------	-------------

Voltage measurement range	50 to 700 V
---------------------------	-------------

Type of measuring instrument	multimeter
------------------------------	------------

Installation, mounting

Mounting type	flush mounted / surface mounted
---------------	---------------------------------

Connection

Connection cross-sect. flexible conductor	2,5 / 6mm ²
---	------------------------

Connection cross-sect. rigid cable	2,5 / 6mm ²
------------------------------------	------------------------

Type of connection	with screw
--------------------	------------

Equipment

Type of display	LCD
-----------------	-----

Digits number	4
---------------	---

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-10...55 °C
Storage/transport temperature	-20...80 °C