



SM151

Digital ammeter 0-150A indirect reading

Technical properties

Architecture

Fixing mode Din-Rail

Functions

Precision class 1%

Configuration

Number of modules 4

Controls and indicators

Measurement scale 150 A

Main electrical features

Rated operational voltage U_e 207 / 230 / 253 V

Frequency 45/65 Hz

Voltage

Voltage drop 120 mV

Dimensions

Depth of installed product 54 mm

Height of installed product 85 mm

Width of installed product 70 mm

Power

Power consumed 1 VA

Total power loss under IN 1 W

Installation, mounting

Modular version Yes

Connection

Connection cross-sect. flexible conductor 6mm²

Connection cross-sect. rigid cable 10mm²

Equipment

Digits number 3

Safety

Protection index IP IP20

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature	-10...55 °C
Storage/transport temperature	-40...70 °C
