



SM151

## Digital ammeter 0-150A indirect reading

### Technical properties

#### Capacity

Number of modules	4
-------------------	---

#### Use conditions

Operating temperature	-10 - 55 °C
Storage/transport temperature	-40 - 70 °C

#### Connection

Cross-section flexible conductor	6 mm <sup>2</sup>
Cross-section rigid conductor	10 mm <sup>2</sup>

#### Dimensions

Height	85 mm
Width	70 mm
Depth	54 mm

#### Measurement

Current measurement range	0 - 150 A
Type of measuring instrument	Digital

#### Power

Power consumption VA	1 VA
Total power loss under IN	1 W

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Installation, mounting

Mounting on	DIN rail
-------------	----------

#### Functions

Accuracy class	0.01
----------------	------

#### Frequency

Frequency	45 - 65 Hz
-----------	------------