



SPB040D

**Cartridge L-N Uc 275V In 20kA I<sub>max</sub> 40kA Up 1,35kV**

**Technical properties**

**Configuration**

Number of modules	1
-------------------	---

**Controls and indicators**

Indicator lamp	Optic
----------------	-------

**Main electrical features**

Rated operational voltage U <sub>e</sub>	240 / 415 V
--	-------------

**Voltage**

Maximum continuous operating voltage U <sub>c</sub>	275 V
---	-------

**Dimensions**

Depth of installed product	58.2 mm
----------------------------	---------

Height of installed product	89.8 mm
-----------------------------	---------

**Electrical specifications**

Short-circuit breaking capacity (I <sub>sc</sub> cr)	25 kA
--	-------

**Installation, mounting**

Tightening torque	3
-------------------	---

**Connection**

Connection cross-section of input and output with screws, for massive conductors	1.5 / 35 mm <sup>2</sup>
--	--------------------------

Connection cross section of access and exit with screws, for flexible conductor	1.5 / 25 mm <sup>2</sup>
---	--------------------------

**Standards**

Test class IEC61643-11 / VDE0675-6-11	T2
---------------------------------------	----

European directive WEEE	concerned
-------------------------	-----------

**Safety**

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

**Use conditions**

Operating temperature	-40...80 °C
-----------------------	-------------