



SPN408S

SPD 4P monobloc 8kA class 2 with light indicator

Technical properties

Configuration

Number of modules 3

Main electrical features

Rated operational voltage U_e 230 / 400 V

Frequency 50/60 Hz

Nominal discharge current (I_n) 8/20 μ s, IEC 61643)L-N(PEN)/ N-PE 2 kA

Voltage

Maximum continuous operating voltage U_c 255 V

Voltage protection level U_p according to IEC61643-1 1 kV

Electric current

Max discharge (I_{max}) L-N(PEN)/ N-PE 8 kA

Dimensions

Width of installed product 54 mm

Power

Total power loss under I_N 0 W

Standards

Test class IEC61643-11 / VDE0675-6-11 T2

European directive WEEE not concerned

Use conditions

Operating temperature -40...60 °C

Storage/transport temperature -40...80 °C