



SR400

Current transformer 400 / 5A

Technical properties

Functions

Precision class	1
-----------------	---

Configuration

Number of modules	4.5
-------------------	-----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Maximum current of primary	480 A
Maximum current of secondary	5 A

Dimensions

Depth of installed product	75 mm
Height of installed product	70 mm
Width of installed product	77 mm
width of opening	10 mm
Height of opening	40 mm

Power

Total power loss under IN	0 W
---------------------------	-----

Connection

Connection cross-sect. flexible conductor	1,5 / 4mm ²
Type of connection	screw

Cable

Cable diameter	35 mm
----------------	-------

Use

Transformation Ratio	400A ; 5A
----------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-25...50 °C
Storage/transport temperature	-40...80 °C