



SRC06005

Bar/Cable-through Current Transformer BG 113 600/5A 5VA Class 1

Technical properties

Functions

Precision class	1
-----------------	---

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Rated insulation voltage	3 kV
--------------------------	------

Electric current

Maximum current of primary	600 A
Maximum current of secondary	5 A
Primary current	600 A

Dimensions

Depth of installed product	30 mm
Height of installed product	70 mm
Width of installed product	50 mm
width of opening	29.5 mm
Height of opening	20 mm
Bar size	30x10 mm / 25x15 mm / 20x20 mm

Power

Total power loss under IN	5.5 W
---------------------------	-------

Connection

Type of connection	screw
--------------------	-------

Accessories included

With copper rail	No
------------------	----

Equipment

Number of inputs	1
With shock protection	Yes

Use

Transformation Ratio	600A ; 5A
----------------------	-----------

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature

-40...40 °C

Storage/transport temperature

-40...40 °C