



ST305



## Bell transformer 16VA 230V 8-12V

### Technical properties

#### Voltage

Output voltage	8 - 12 V
Rated operational voltage Ue	230 - 230 V
Output voltage 2	12 V
Rated insulation voltage Ui	4000 V

#### Capacity

Number of modules	3
-------------------	---

#### Power

Power consumption VA	16 VA
Power	16 VA
Power absorbed	16 W

#### Dimensions

Height	111 mm
Width	54 mm
Depth	65 mm
Length	64 mm

#### Safety

Ingress Protection (IP) class	IP20
Temperature protection	Yes

#### Equipment

Is short-circuit protected	Yes
On/off switch	No

#### Use conditions

Operating temperature	-20 - 35 °C
-----------------------	-------------

#### Connection

Cross-section flexible conductor	4 mm <sup>2</sup>
Cross-section rigid conductor	6 mm <sup>2</sup>

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Electric current

Intensity output 1	2 A
Intensity output 2	1,33 A

**Installation, mounting**

---

Mounting on DIN rail

Nominal tightening torque 1,20 - 1,20 Nm

**Internal use only**

---

Number of half modules of 17,5 mm 6

**Compatibility**

---

Suitable for DIN Rail Yes