



SU212



**Bell 12V**

**Technical properties**

**Architecture**

Fixing mode DIN rail type O (symmetrical)

**Configuration**

Number of modules 1

**Main electrical features**

Rated operational voltage Ue 8 / 12 V

Type of supply voltage AC

**Electric current**

Operating current 0.33 A

Rated current 0.33 A

**Dimensions**

Depth of installed product 65 mm

Height of installed product 80 mm

Width of installed product 18 mm

**Frequency**

Frequency 50 to 0 Hz

**Power**

Power consumed 5 VA

Total power loss under IN 5 W

**Materials**

Material polyamide

**Equipment**

Noise level 85 dB

**Standards**

European directive WEEE concerned

**Safety**

Protection index IP IP20

**Use conditions**

Operating temperature -10...40 °C

Storage/transport temperature -25...60 °C