



SU213



## Bell 230V

### Technical properties

#### Electric current

Rated current	0,03 A
---------------	--------

#### Dimensions

Height	80 mm
Width	18 mm
Depth	65 mm

#### Use conditions

Operating temperature	-10 - 40 °C
Storage/transport temperature	-25 - 60 °C

#### Connection

Cross-section flexible conductor	4 mm <sup>2</sup>
Cross-section rigid conductor	6 mm <sup>2</sup>

#### Power

Total power loss under IN	6,50 W
Power consumption VA	6,50 VA

#### Equipment

Noise level	85
-------------	----