



SVN121M

## Green LED Indicator light 230VAC

### Technical properties

#### Capacity

Number of modules	1
-------------------	---

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Voltage

Rated insulation voltage $U_i$	250 V
Rated impulse withstand voltage $U_{imp}$	4000 V
Type voltage supply	AC
Rated operational voltage $U_e$	230 - 230 V

#### Use conditions

Operating temperature	-20 - 50 °C
Storage/transport temperature	-40 - 80 °C

#### Connectivity

Type of connection	Screw terminal
--------------------	----------------

#### Connection

Cross-section flexible conductor	0.75 - 6 mm <sup>2</sup>
Cross-section rigid conductor	0.75 - 10 mm <sup>2</sup>
Type of lamp socket	Fix

#### Power

Total power loss under $I_N$	0,80 W
Power per charging point	0

#### Dimensions

Height	83 mm
Width	17,50 mm
Depth	62 mm

#### Lighting

Type of lamp	LED
--------------	-----

#### Materials

Colour	Green
--------	-------

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------