



SVN124M

Blue LED Indicator light 230VAC

Technical properties

Capacity

Number of modules	1
-------------------	---

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated insulation voltage U_i	250 V
Rated impulse withstand voltage U_{imp}	4000 V
Type voltage supply	AC
Rated operational voltage U_e	230 - 230 V

Use conditions

Operating temperature	-20 - 50 °C
Storage/transport temperature	-40 - 80 °C

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Connection

Cross-section flexible conductor	0.75 - 6 mm ²
Cross-section rigid conductor	0.75 - 10 mm ²
Type of lamp socket	Fix

Power

Total power loss under IN	0,80 W
Power per charging point	0

Dimensions

Height	83 mm
Width	17,50 mm
Depth	62 mm

Lighting

Type of lamp	LED
--------------	-----

Materials

Colour	Blue
--------	------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------