



TGA200



Power supply 24 V DC 1A

Technical properties

Architecture

Bus system	EIB
------------	-----

Configuration

Number of modules	4
-------------------	---

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Output voltage	24 V DC
----------------	---------

Output voltage	24 V
----------------	------

Filtered output voltage	24V +/- 5%
-------------------------	------------

Electric current

Output current	1 A
----------------	-----

Dimensions

Depth of installed product	64 mm
----------------------------	-------

Height of installed product	90 mm
-----------------------------	-------

Width of installed product	72 mm
----------------------------	-------

Power

Current consumption	150 mA
---------------------	--------

Power consumed	16 VA
----------------	-------

Power consumption (standby)	0.2 W
-----------------------------	-------

Total power loss under IN	15 W
---------------------------	------

Measurement

Voltage measurement range	22.8 to 25.2 V
---------------------------	----------------

Materials

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Installation, mounting

Modular version	Yes
-----------------	-----

Suitable for front mounting	No
-----------------------------	----

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
---	---------------------------

Connection cross-sect. rigid cable	0,75 / 2.5mm ²
------------------------------------	---------------------------

Type of connection	with QuickConnect plug-in terminals
Type of connection	Quickconnect
Equipment	
Short-circuit protected	Yes
Use	
Differentiation characteristic 1 - Sales	with labelling field
Safety	
REACH conform	No
RoHS conform	Yes
Halogen free	No