



TN002S

Cat 6 STP Data patch module

Technical properties

Architecture

Type RJ45 8(8)

Configuration

Module VDI

Connectivity

Passband 250 MHz (900MHz for TV signal)

Connection

Type of connection insulation displacement

Cable

AWG range AWG 26-22

Equipment

Screened Yes

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Identification

Category Cat6