



TXA100

IP20

easy configuration tool kit

Technical properties

Controls and indicators

Manual selection switches / push-buttons	Selection switch for online/offline mode
Button / push-button	with programming button and red programming LED

Voltage

Operating voltage	230 V AC
Operating voltage over bus	21...32 V DC

Dimensions

Dimensions (LLxwxhh)	41.5x33x10 cm
----------------------	---------------

Connection

Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

Scope of delivery

Bus connection included	Yes
Contents of the kit	Configuration tool + WIFI access point + Power supply 1x 30VDC + 1x 24VDC

Equipment

Updateable	Yes
Visualization	No
Web-Server	Yes

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C

Identification

Main design line	KNX
------------------	-----

Instructions

Information text	Network technology skills are required for commissioning. System requirements: Windows 8.1, Android 4.4, iOS 8.
------------------	---