



TXA100



IP20

easy configuration tool kit

Technical properties

Configuration

Category / ports RJ45 Port for LAN connection

Controls and indicators

Manual selection switches / push-buttons Selection switch for online/offline mode

Button / push-button with programming button and red programming LED

Connectivity

Ethernet data rate max. 2 x 100/1000 Mbit/s

Connectors / jacks with 2 USB jacks type B, USB 2.0 compliant

Voltage

Operating voltage 230 V AC

Operating voltage over bus 21...32 V DC

Dimensions

Dimensions (LLxwxh) 41.5x33x10 cm

LED control

LED with green and red status LED for LAN status, operational stand-by, KNX status and gateway connection

Connection

Bus coupling unit with integral bus coupling unit

Bus connection bus connection via connecting terminal

Connection with two RJ45 jacks ; for connection to a 230 V AC socket outlet

Settings

Supported configuration modes easy

Scope of delivery

Bus connection included Yes

Contents of the kit Configuration tool + WIFI access point + Power supply 1x 30VDC + 1x 24VDC

Equipment

Updateable Yes

Visualization No

Web-Server Yes

Software

Software

portable case with complete set for commissioning
of KNX installations in easy mode

Use conditions

Operating temperature

0...45 °C

Storage/transport temperature

-20...70 °C

Identification

Main design line

KNX

Instructions

Information text

Network technology skills are required for
commissioning. System requirements: Windows 8.1,
Android 4.4, iOS 8.