



TXA111

IP20

Power supply 30V DC 320 mA

Technical properties

Architecture

Bus system EIB

Configuration

Number of modules 4

Connectivity

Bus lines 1

Main electrical features

Frequency 50/60 Hz

Voltage

Output voltage 30 V

Output voltage 28...32 V

Filtered output voltage 30V +/- 2V

Electric current

Output current max. 320 mA

Output intensity 320 mA

Dimensions

Depth of installed product 64 mm

Height of installed product 90 mm

Length 64 mm

Width of installed product 72 mm

Power

Total power loss under IN 15 W

Materials

RAL colour RAL 7035 - Light grey

Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm²

Connection cross-sect. rigid cable 0,75 / 2.5mm²

Conductor cross-section (flexible) 0.75...2.5 mm²

Conductor cross-section (rigid) 0.75...2.5 mm²

Type of connection quick connect

Use

Use conditions

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C
