



TYA606A



Output module 6x 4A /230V~, KNX

Technical properties

Architecture

Fixing mode REG

Functions

Multi-phase mode suitable to switch different external conductors

Configuration

Number of modules 4

Controls and indicators

Manual selection switches / push-buttons manual operation buttons for on/off (up/down) and bus function on/off per channel/device

Button / push-button with illuminated programming button

Main electrical features

Rated current 4 A

Voltage

Operating voltage over bus 21...32 V DC

Output voltage 230 V~

System supply voltage 30V DC via bus

Electric current

Bus current consumption (data transfer) 4 mA

Bus current consumption (idle) 3 mA

Number of entry circuits 0

Maximum through current 4 A

Switching current at $\cos \varphi = 0.8$ max. 4 A

Dimensions

Depth 65 mm

Width of rail mounted device (RMD) 4 modules

Height 90 mm

Power

Max. power with electronic transfo. 800 W

Total power loss under IN 1 W

Output power 800 W

Conventional transformers 800 VA

Electronic transformers 800 W

Materials

Colour	light grey
--------	------------

Fluorescent bulbs control

Energy-saving lamps	6 x 23 W
Power lighting fluo lamps	6x23W
Max. power fluo. duo lamp comp. series	12 x 36 W

LED control

Max number of LED/CFL lamps	6
Power LED	72 W

Incandescent bulbs control

Max. power with incandescent lamps	800 W
230 V incandescent lamps	800 W
230 V halogen lamps	800 W
230 V incandescent lamps and halogen lamps	800 W

Connection

Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

Settings

Supported configuration modes	system
-------------------------------	--------

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Modular expandability	No
-----------------------	----

Use

Differentiation characteristic 3 - Sales	with plug-in terminals
--	------------------------

Safety

Protection index IP	IP20
REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C

Identification

Main design line	KNX
------------------	-----