



TYF130



**Line coupler, KNX**

**Technical properties**

**Architecture**

Fixing mode Din-Rail

**Functions**

Easy link functions can be used as line amplifier

**Configuration**

Number of modules 2

**Controls and indicators**

Button / push-button with programming button and red programming LED

**Voltage**

Operating voltage over bus 21...32 V DC

System supply voltage 30V DC via bus

**Dimensions**

Width of rail mounted device (RMD) 2 modules

**Power**

Total power loss under IN 0.5 W

**Connection**

Type of connection to the bus TG008 connector

Bus coupling unit with integral bus coupling unit

Bus connection bus connection via connecting terminal

**Settings**

Supported configuration modes system

**Use conditions**

Operating temperature -5...45 °C

**Identification**

Main design line KNX