



VD104NT

Sm.distr.,VD/IC²,surface,1row,4M,IP30,no terminals,AUS,without door

Technical properties

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	4
-------------------	---

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	71 mm
----------------------------	-------

Internal depth	72 mm
----------------	-------

Height of installed product	163.5 mm
-----------------------------	----------

Width of installed product	81.5 mm
----------------------------	---------

Width in division units	4
-------------------------	---

Cover, door

Type of door closing	non keylock
----------------------	-------------

Interlockable	No
---------------	----

Number of keylock of the door	0
-------------------------------	---

Cover type	Closed (plain)
------------	----------------

Transparent cover or door	No
---------------------------	----

Materials

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	plastic
----------	---------

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	1
----------------	---

Quantity of section in width	1
------------------------------	---

Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	No
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	Yes

Safety

IK protection code against mechanical impacts	IK07
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------